

# >> DE-R 263 - Standard Diffractive Optical Element

**Element Number: DE-R 263**

Description: 1 : 5 Dot Line


Number of Dots: 5 Dots

Material: Polycarbonate (PC)

Size ( $\varnothing$  x Thickness): 8 x 1.2 mm

Optimum Wavelength: **650 nm**


(The element is usable with a range of wavelengths, but the following parameters will vary most with the wavelength: pattern size (see table 1) and intensity in the undiffracted central spot ('zero order', see table 2). At the optimum wavelength given on this datasheet, the element shows the same intensity in the central spot as in the off-axis spots.)




**Table 1**

Wavelength	Pattern Size @ 100 mm Distance		Pattern Angles	
	a	b	$\alpha$	$\beta$
488 nm	8.1 mm	2.0 mm	4.6 mm	1.15 mm
543 nm	9.0 mm	2.2 mm	5.1 mm	1.28 mm
594 nm	9.8 mm	2.5 mm	5.6 mm	1.40 mm
635 nm	10.5 mm	2.6 mm	6.0 mm	1.50 mm
<b>650 nm</b>	<b>10.7 mm</b>	<b>2.7 mm</b>	<b>6.1 mm</b>	<b>1.54 mm</b>
730 nm	12.1 mm	3.0 mm	6.9 mm	1.73 mm
780 nm	12.9 mm	3.2 mm	7.4 mm	1.84 mm
808 nm	13.4 mm	3.4 mm	7.6 mm	1.91 mm

## Setup:



## Diffraction Zero Order Intensity:



**Table 2**

Wavelength	0th Order Intensity
488	34%
543	23%
594	16%
635	12%
<b>650</b>	<b>11%</b>
730	11%
780	13%
808	14%